

Ideal for temperature measurement, monitoring and management of temperature data records

# Thermometers

## TM10,20 / TX10

■ The TM Series offers excellent data management functions

- Collect up to 5000 data items with time-stamp, tag name and inspector name.
- Save 2 weeks continuous data logging with 1 minute interval, (up to 20000 data items, measuring interval is 1sec. to 24 hours.)  
Information on **when** , **by whom** and **what** is measured is saved along with the data.

■ The simplicity of the TX10 Series allows for ease of use.

- For K, E, J, and T type thermocouples
- Easy display switching between channels A and B



TM10  
Thermistor Input

TM20  
Thermocouple Input



Improved data management with inclusion of information on **when**, **by whom** and **what** is measured

# TM Series of Thermo-Collectors

TM10 for Food & HACCEP use  
TM20 for Industrial use

**TM10**

Thermistor model

Effective for HACCP program implementation

## TM10/TM20 Common Features

External probes (-30°C to 200°C) [-22°F to 392°F]

There are three types available: a needle probe for mid-point temperature, a rounded end probe for liquid temperature, and a surface probe for surface temperature.

Built-in sensor (-20°C to 50°C) [-4°F to 122°F]

Measures ambient temperature, and allows for continuous measurement inside a warehouse or during transportation.

### Memory key

Each press of this key saves the measured data, along with 3 other monitoring items: the name of the object being measured, operator's name, and date and time of measurement.

### Selection of registered tag name

Select from the list of up to 50 registered tag names (objects to be measured).

### Input selection key

### Collector/Logging mode selector key

Switches between the collector mode (saves measured data when necessary) and logging mode (saves measured data continuously).

- When used in the collector mode only, saves up to 5000 data items.\*
- When used in the logging mode only, saves up to 20000 data items.\*

Measuring interval: 1 second to 24 hours (Under simultaneous 2-channel measurement with the TM20, 2 seconds is the minimum.)

Start-of-measurement time: timer can be set.

\* Under simultaneous 2-channel measurement, the TM20 saves 2 data items for one measurement.

### User-friendly FUNC key

You can select setup items in the same way as you choose options from the built-in menu of a cellular phone.

### Selection of operator name

With the (1) key, you can recall a list of up to 10 operator names and can also change any of these names.

### Record-keeping on measurement failure handling

By pre-registering a list of up to 32 comments on how to handle particular measurement failures, you can keep records of how the measurement failure was dealt with by selecting the desired comment from the list using the (4) key.

(The TM10 supports this feature with TM10 Version 1.10 when used with application software version 1.30 or later.)

### Setup keys

Register tag names, set alarm points, and define measuring conditions, such as the measuring interval for the logging mode. These setting tasks can also be carried out from a PC.

### Digital input terminal

For connecting to an optional non-contact probe.

### RS-232C I/O terminals

Used to exchange data with a PC or send data to a dedicated printer.



Full Size

Light Weight: 170 g

### Drip-proof construction (TM10/TM20)

Conforming to IP54 standards, the TM10/TM20 can still function even if it becomes wet to some degree. In addition, the optional waterproof cover increases waterproofing and protects the instrument against possible dirt contamination.

### IP 5 4

Drip-proof: Immune to any harmful effects from liquid splashes from any direction.

Dust-proof: Prevents dust from entering the instrument.

**TM20**

**Universal dual inputs model**

Simultaneous 2-channel measurement with thermocouple probes  
**You can select from types K, E, J, and T to change probes according to sensor type.**



**Thermocouple probes (-200°C to 1372°C) [-328°F to 2501.6°F]**

- Type K : -200°C to 1372°C [-328°F to 2501.6°F]
  - Type E : -200°C to 700°C [-328°F to 1292°F]
  - Type J : -200°C to 1000°C [-328°F to 1832°F]
  - Type T : -200°C to 400°C [-328°F to 752°F]
- (Possible temperature ranges with the TM20)

**Analog signal input**

The TM20 can accept inputs from a sensor that outputs voltage signals ranging  $\pm 100$  mV or  $\pm 1$  V.  
 \* A U-shaped Miniature connector is required.


Full Size

Light Weight: 180 g

**● Products that can be connected to the TM20**

- Connecting the TM20 to various analog output sensors allows for data storage and management.
- The TM20 also has a scaling function that shows computed values on its display.



**Model 900 01/U temperature and humidity probe**



TM20-dedicated probe that connects via a U-shaped Miniature connector

**Digital illuminance meters (510 Series)**

**Model 310 03 leak clamp tester**

**● Waterproof Cover and Soft Carrying Case**

**Waterproof cover**  
**Model 930 11 (for TM10/TM20)**

With the waterproof cover, you can keep the TM10 clean and increase its waterproofing qualities.



**Soft Case**  
**Model 930 10 (for TM10)**  
**Model 930 12 (for TM10/TM20)**

Can be attached to your belt.






# Data management is made easy because the TM10/TM20 records data items that tell you **when**, **by whom**, and **what** along with the temperature data.


## Easy data management using a PC (data management software included)

Setting measurement conditions from the PC.

(1) Download the measurement conditions to the TM10/TM20.



(2) Carry out measurement.




(3) Upload the measured data to the PC.


- Microsoft Excel spreadsheets are automatically generated for each object being measured (tag name) and each date of measurement. Data collected later can also be added to these spreadsheets. The TM10 supports this feature with TM10 Version 1.10 when used with application software version 1.30 or later.

## Configuration of a system based on the TM10/TM20 Thermo-collector


### ● Probes for contact thermometry



### ● Probes for non-contact thermometry



### ● Data management based on easy-to-use application software (The software is supplied together with the TM10/TM20.)




Real-time transmission is possible.\*  
The measured data can be transmitted to the PC in real-time during measurement.



\* When performing real-time transmission, always use the non-contact probe.

RS-232C interface cables:  
Model 910 11 (with 8-pin barrel and 9-pin D-sub connectors)

### ● Data management through direct printing



Model 910 10 RS-232C interface cable (with 8-pin barrel and 9-pin D-sub connectors)  
Model 970 10 dedicated printer  
External dimensions: 160 x 170 x 66.5 mm

| Product name (Model)                          | TM10 Thermo-collector<br>Thermistor model<br>(540 51)   | TM20 Thermo-collector<br>Thermocouple model<br>(540 11)  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
|---|---|--|----------|---------------------|--|-----------------------|----------|-----------------------|----------|------------------|--------|----------------|--------|-----------------|--------|---------------|--------|---------------|--------|----------------|--------|------------------|--------|--|--|------------------|--------|--|--|--|
| Number of measuring channels                  | 1 (Selectable from 3 channels)<br>One channel is provided for each of the external thermistor probe, built-in thermistor sensor, and external non-contact probe.  | 2 (when A and B channels are used for thermocouple or voltage input)<br>1 (when D channel is used with the non-contact probe)  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Measuring range (only the main unit)          | External thermistor -30°C to 200°C [-22°F to 392°F]<br>Built-in thermistor -20°C to 50°C [-4°F to 122°F]<br>Thermal emission (external probe) -20°C to 400°C [-4°F to 752°F]  | Thermocouple Type K : -200°C to 1372°C [-328°F to 2501.6°F]<br>Type J : -200°C to 1000°C [-328°F to 1832°F]<br>Type E : -200°C to 700°C [-328°F to 1292°F]<br>Type T : -200°C to 400°C [-328°F to 752°F]<br>Thermal emission -20°C to 400°C [-4°F to 752°F]<br>Voltage input ±100 mV, ±1 V |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Resolution                                    | External thermistor: 0.1°C<br>Built-in thermistor: 0.1°C<br>Thermal emission (external probe): 1°C  | Thermocouple: 0.1°C<br>Thermal emission: 1°C<br>Voltage input: 0.1 mV or 0.001 V   |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Accuracy (only the main unit)                 | <table border="1"> <thead> <tr> <th colspan="2">External thermistor</th> <th colspan="2">Built-in thermistor</th> </tr> <tr> <th>Temperature range (T)</th> <th>Accuracy</th> <th>Temperature range (T)</th> <th>Accuracy</th> </tr> </thead> <tbody> <tr> <td>-30.0 to -19.9°C</td> <td>±1.0°C</td> <td>-20.0 to 0.0°C</td> <td>±1.0°C</td> </tr> <tr> <td>-20.0 to -0.0°C</td> <td>±0.4°C</td> <td>0.1 to 39.9°C</td> <td>±0.8°C</td> </tr> <tr> <td>0.1 to 99.9°C</td> <td>±0.3°C</td> <td>40.0 to 50.0°C</td> <td>±1.0°C</td> </tr> <tr> <td>100.0 to 149.9°C</td> <td>±0.4°C</td> <td></td> <td></td> </tr> <tr> <td>150.0 to 200.0°C</td> <td>±0.7°C</td> <td></td> <td></td> </tr> </tbody> </table> <p>* For the accuracy when using a non-contact probe (900 03), see the accuracy ratings of the probe.</p> | External thermistor  |          | Built-in thermistor |  | Temperature range (T) | Accuracy | Temperature range (T) | Accuracy | -30.0 to -19.9°C | ±1.0°C | -20.0 to 0.0°C | ±1.0°C | -20.0 to -0.0°C | ±0.4°C | 0.1 to 39.9°C | ±0.8°C | 0.1 to 99.9°C | ±0.3°C | 40.0 to 50.0°C | ±1.0°C | 100.0 to 149.9°C | ±0.4°C |  |  | 150.0 to 200.0°C | ±0.7°C |  |  | Thermocouple -200.0 to 100.1°C : ±(0.1% of rdg + 0.7°C)<br>-100.0°C or above : ±(0.1% of rdg + 1.0°C)<br>*Accuracy of reference junction compensation is included ±0.4°C when the temperature of the input terminal is in equilibrium.<br>Thermal emission ±(1% of rdg + 1°C) or ±3°C, depending on the accuracy of the non-contact probe.<br>Voltage input ±(0.1% of rdg + 0.2% of range) |
| External thermistor                           |   | Built-in thermistor  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Temperature range (T)                         | Accuracy  | Temperature range (T)  | Accuracy |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| -30.0 to -19.9°C                              | ±1.0°C  | -20.0 to 0.0°C   | ±1.0°C   |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| -20.0 to -0.0°C                               | ±0.4°C  | 0.1 to 39.9°C  | ±0.8°C   |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| 0.1 to 99.9°C                                 | ±0.3°C  | 40.0 to 50.0°C   | ±1.0°C   |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| 100.0 to 149.9°C                              | ±0.4°C  |  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| 150.0 to 200.0°C                              | ±0.7°C  |  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Measuring mode                                | Collector mode or Logging mode  |  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Measuring interval                            | Collector mode: 1 second or longer<br>Logging mode: 1 second to 24 hours  | Collector mode: 0.5 seconds or longer when 1 channel is used.<br>1 second or longer when 2 channels are used.<br>Logging mode: 1 second to 24 hours when 1 channel is used.<br>2 seconds to 24 hours when 2 channels are used.   |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Data capacity                                 | 5000 data items when used in collector mode only.<br>20000 data items when used in logging mode only.<br>Measurement data obtained in collector mode and logging mode can coexist.  | 5000 data items when used in collector mode only.<br>20000 data items when used in logging mode only.<br>Measurement data obtained in collector mode and logging mode can coexist.<br>Under simultaneous 2-channel measurement, 2 data items are recorded at the same time.                |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Drip-proof construction                       | Conforms to IP54 standards (dust-proof and drip-proof requirements of IEC529)   |  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Display                                       | LCD with backlight  |  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Operating temperature and humidity            | -20°C to 50°C, 20 to 80% RH (no condensation)   | 0°C to 50°C, 20 to 80% RH (no condensation)  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Power requirements                            | Two AA-size alkaline dry batteries (LR6)  |  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Battery life                                  | Approx. 3 months when operated in logging mode at 10-minute intervals;<br>Approx. 1 month when operated in logging mode at 1-minute intervals;<br>Approx. 2 weeks when operated in collector mode 8 hours a day.  | Approx. 1.5 months when operated in logging mode at 10-minute intervals;<br>Approx. 1 month when operated in logging mode at 1-minute intervals;<br>Approx. 5 days when operated in collector mode 8 hours a day including 30 minutes of communication.                                    |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Registration of tag names                     | A maximum of 50, each comprising up to 8 alphanumeric characters  |  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Registration of operator names                | A maximum of 10, each comprising up to 8 alphanumeric characters  |  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Registration of comments                      | A maximum of 32, each comprising up to 8 alphanumeric characters  |  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Alarm function                                | Upper- and lower-limit alarms   |  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Computing function                            | Maximum, minimum, and average   | Maximum, minimum, and average<br>Reading of difference between the 2 channels is possible.   |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Communication function                        | Conforms to EIA RS-232C standard.   |  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Simplified correction function                | None  | Corrects the measured data from thermocouple input within the range of ±20.0°C.  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Scaling function                              | None  | Scales the voltage input x according to the formula "Ax + B," which is defined from the thermo-collector software.   |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Other functions                               | Chime, function lock, clock display, auto power-off, and battery alarm  |  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Thermo-collector software system requirements | CPU: i486DX or higher<br>OS: Windows 95/Windows 98/Windows NT 4.0<br>FDD: 3.5", 1.44 MB-formatted<br>Required space on the HDD: 10 MB or greater  | Recommended memory capacity: 16 MB or greater<br>Serial I/O capability: A serial port conforming to RS-232C standard should be available.<br>Software: Microsoft Excel 95, Microsoft Excel 97  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Compliance with standards                     | EMC standards   | EMI (interference signal): EN55011;1998, EN61326-1;1998+A1 (Class B, Group 1)<br>EMS (immunity): EN50082-1;1997, EN61326;1998+A1   |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| External dimensions                           |  <p>Approx. 133(H) × 56(W) × 33(D) mm (excluding protrusions)<br/>Weight: Approx. 170 g (including batteries)</p>  |  <p>Approx. 151(H) × 56(W) × 33(D) mm (excluding protrusions)<br/>Weight: Approx. 180 g (including batteries)</p>  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Supplied accessories                          | Software, two AA-size alkaline dry batteries (LR6), a waterproof cover, and an instruction manual   |  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
| Optional accessories                          | Standard needle probe (900 10)<br>High-speed needle probe (900 11)<br>Surface probe (900 12)<br>Rounded end probe (for liquid) (900 13)<br>Soft case (930 10)   | Temperature probes (for K type thermocouple):<br>Rounded end probe (900 20, 900 21, 900 22)<br>Needle probe (900 23, 900 24)<br>Surface probe (900 30, 900 31, 900 32, 900 33)<br>Bead TC (2459 07)<br>Extension cable 5 m (2459 21) / 10 m (2459 22)<br>Soft case (930 12)                |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |
|   | Non-contact probe (900 03) ●RS-232C cable for PC connection:9-pin (910 11) ●AC adapter for printer:Europe (940 06) / USA (940 07)<br>●Printer (970 10) ●RS-232C cable for printer connection (910 10) ●Thermal paper for printer (10 rolls) (970 80)●Waterproof cover (5 per package) (930 11)  |  |          |                     |  |                       |          |                       |          |                  |        |                |        |                 |        |               |        |               |        |                |        |                  |        |  |  |                  |        |  |  |  |



Simplicity Allows for Ease of Use

# TX10 Series of Digital Thermometers

TX10 Series offers thermocouple thermometers that support K, J, E and T type thermocouples. There are three models available: 1-channel single-function, 1-channel multi-function, and 2-channel multi-function models.

**TX10  
-01**



## 1-channel Single-function Model (TX10-01)

### TC TYPE

Select the thermocouple type (K, J, E, and T) for the initial setting.  
(The type K is factory-set at shipment)

### Operation

Press and hold down the TC TYPE key while pressing the POWER key.  
The TX10 enters the thermocouple type selection mode, and each press of the TC TYPE key switches between the thermocouple types.  
Then accept the setting with the POWER key.  
(Make sure that the characters in the display have changed.)

### DATA HOLD

Press this key to hold the measured value.

## Multi-function Models (TX10-02/-03)

### Memory-in Function

Up to ten data items can be stored. When recalled, the stored data value is displayed with its memory number.

### User calibration function

Calibration and adjustment can be made easily by operating the panel keys on instrument and a measurement-standard.

**TX10  
-02/-03**



### TC TYPE

**Thermocouple type (K, J, E, and T) select key**  
(Operation is the same as TX10-01)

### CH

(TX10-03 only)

### Input channel select key

With each press, the channel switches through the sequence of "chA," "chB," and then "chA-chB."

### DATA HOLD

### Data hold key

A held measured value, can be stored in the memory of an optional memory number, which is selected with the ▲, ▼ keys.

### RECORD

### Maximum and minimum record key

Stores the maximum and minimum values from the time the RECORD key is pressed.

### Data record key

Stores the held measured value in memory. (Up to ten)

### RANGE

### Resolution select key

With each press, resolution alternates between 0.1°C and 1°C.  
(Within the range of -200.0°C to 199.9°C)

### READ

### Maximum and minimum values, and stored data read key

Every time this key is pressed, the maximum and minimum values, stored data, and the current measured data are displayed in sequence.

### REL/ADJ

### Relative display select key

Displays measured values with reference to the value obtained immediately before this key was pressed (relative value). Each press of this key can select or release the relative display.

### Simplified correction mode key

Sets the correction value, and selects active/inactive of the simplified correction function.

### ▲, ▼ Data call-up key

Used to select a memory number when calling up stored data. Also used to adjust the correction value for simplified correction mode.

Light  
Weight:  
180 g

(Shown above is the TX10-03. The TX10-02 has no CH key.)

## Can Be Used in Wide Variety of Applications



● Temperature management in a refrigerated warehouse



● Frozen food products quality control



● Perishable foods quality control



● Temperature management in production processes



● Product temperature measurement test



● Temperature checks in equipment maintenance  
● Temperature management for research and development

| Product name                         | Digital Thermometer  |  |   |
|--------------------------------------|--|--|---|
|                                      | Single-function, 1 channel   | Multi-function, 1 channel  | Multi-function, 2 channels  |
| Model                                | TX10-01  | TX10-02  | TX10-03   |
| Number of input channels             | 1  |  | 2   |
| Measuring range (only the main unit) | Thermocouple type<br>Type K: -200°C to 1372°C [-328°F to 2501.6°F]<br>Type J: -200°C to 1000°C [-328°F to 1832°F]  | Type E: -200°C to 700°C [-328°F to 1292°F]<br>Type T: -200°C to 400°C [-328°F to 752°F]  |   |
| Resolution                           | -200.0°C to 199.9°C: 0.1°C<br>200°C or above: 1°C  | -200.0°C to 199.9°C: 0.1°C or 1°C (when 1°C resolution is set)<br>+200°C or above: 1°C   |   |
| Accuracy (only the main unit)        | -200.0°C to -100.1°C: ±(0.1% of rdg + 1.0°C)<br>-100.0°C to 199.9°C: ±(0.1% of rdg + 0.7°C)<br>+200°C or above, or when 1°C resolution is set: ±(0.2% of rdg + 1°C)  |  | *Accuracy of reference junction compensation is included ±0.4°C when the temperature of the input terminal is in equilibrium. |
| Temperature coefficient              | ±(0.015% of rdg + 0.06°C)/°C   |  |   |
| Measurement interval                 | Approx. 1 sec.   |  | Approx. 1 sec. (1 channel measurement)<br>Approx. 2 sec. (2 channel measurement)  |
| Data storage                         | None   | Capable of storing up to 10 measured data items  |   |
| Simplified correction                | None   | Correction range: ±20°C of measured value  |   |
| Display items                        | HOLD, °C, ch A, TC type K, J, E, T, Battery alarm  | HOLD, RCD, REL, ADJ, MAX, MIN, MEM, °C<br>chA, TC type K, J, E, T<br>Battery alarm   | HOLD, RCD, REL, ADJ, MAX, MIN, MEM, °C<br>chA, chB, chA-chB<br>TC type K, J, E, T<br>Battery alarm                            |
| Other functions                      | Auto power-off, battery alarm  |  |   |
| Display                              | LCD  |  |   |
| Operating temperature and humidity   | 0°C to 50°C, 20 to 80% RH (no condensation)  |  |   |
| Power requirements                   | Two AA-size alkaline dry batteries (LR6)   |  |   |
| Battery life                         | About 450 hours  |  |   |
| Drip-proof construction              | Conforms to IP54 (dust-proof and drip-proof requirements of IEC529)  |  |   |
| Compliance with standards            | EMC standards  | EMI (interference signal): EN55011;1998, EN61326-1;1998+A1 (Class B, Group 1)<br>EMS (immunity): EN50082-1;1997, EN61326;1998+A1 |   |
| External dimensions                  | <p style="text-align: center;">Approx. 151(H) × 56(W) × 33(D) mm (excluding protrusions)    Weight: Approx. 180 g (including batteries)</p>  |  |   |
| Supplied accessories                 | Two AA-size alkaline dry batteries (LR6) and instruction manual  |  |   |
| Optional accessories                 | Temperature probes (for K type thermocouple)<br>Rounded end probe (900 20, 900 21, 900 22)<br>Needle probe (900 23, 900 24)<br>Surface probe (900 30, 900 31, 900 32, 900 33)<br>Bead TC (2459 07)<br>Extension cable 5 m (2459 21) /10 m (2459 22)<br>Soft case (930 12)<br>Waterproof cover (5-per package) (930 11) |  |   |

## Specifications of Accessories

### Probes for TM10

900 10 Standard Needle Probe  
900 13 Rounded end Probe (for Liquid)

● Measuring range: -30°C to 200°C [-22°F to 392°F]

| Temperature range (T) | Accuracy         |
|-----------------------|------------------|
| -30°C ≤ T < -20°C     | ±1.0°C (Typical) |
| -20 ≤ °C ≤ 0          | ±0.5°C (Typical) |
| 0 < °C < 100          | ±0.5°C           |
| 100 ≤ °C < 150        | ±1.0°C (Typical) |
| 150 ≤ °C ≤ 200        | ±2.0°C (Typical) |

● Response: Approx. 6 seconds for 90% of final value

900 03 Non-contact probe

● Measuring range: -20°C to 400°C [-4°F to 752°F]  
● Accuracy: ±1% of reading ±1°C or ±3°C whichever is greater.

● Response: 0.8 seconds for 90% of final value

900 11 High-speed Needle Probe  
900 12 Surface Probe

● Measuring range: -30°C to 200°C [-22°F to 392°F]

| Temperature range (T) | Accuracy         |
|-----------------------|------------------|
| -30°C ≤ T < -20°C     | ±2.0°C (Typical) |
| -20 ≤ °C ≤ 0          | ±1.5°C (Typical) |
| 0 < °C < 100          | ±1.5°C (Typical) |
| 100 ≤ °C < 150        | ±1.5°C (Typical) |
| 150 ≤ °C ≤ 200        | ±2.5°C (Typical) |

● Response: Approx. 2 seconds for 90% of final value (900 11)

Approx. 6 seconds for 90% of final value (900 12)

Note: The accuracy ratings above were obtained with the measurement of liquids being agitated.

### Probes for TM20/TX10

Temperature Probe (for type K)

| Model   | Probe type       | Measuring range             | Accuracy                | Response time (second) | Sensor Diameter / Length (mm) | Cord length |
|---------|------------------|-----------------------------|-------------------------|------------------------|-------------------------------|-------------|
| 900 20  | rounded end      | -50 to 600°C[-58 to 1112°F] | 0.4% or ±1.5°C(±2.7°F)  | 1.4                    | φ3.2 / 200                    | 1.2 m       |
| 900 21  | rounded end      | -50 to 600°C[-58 to 1112°F] | 0.4% or ±1.5°C(±2.7°F)  | 0.4                    | φ1.6 / 150                    | 1.2 m       |
| 900 22  | rounded end      | -50 to 600°C[-58 to 1112°F] | 0.4% or ±1.5°C(±2.7°F)  | 1.4                    | φ3.2 / 500                    | 1.2 m       |
| 900 23  | needle           | -50 to 500°C[-58 to 932°F]  | 0.4% or ±1.5°C(±2.7°F)  | 0.4                    | φ1.6 / 100                    | 1.2 m       |
| 900 24  | needle           | -50 to 500°C[-58 to 932°F]  | 0.4% or ±1.5°C(±2.7°F)  | 1                      | φ2.1 / 100                    | 1.2 m       |
| 900 30  | Surface straight | -20 to 250°C[-4 to 482°F]   | 0.75% or ±2.5°C(±4.5°F) | 2                      | φ15 (temp. sensing portion)   | 1.2 m       |
| 900 31  | Surface angled   | -20 to 250°C[-4 to 482°F]   | 0.75% or ±2.5°C(±4.5°F) | 2                      | φ15 (temp. sensing portion)   | 1.2 m       |
| 900 32  | Surface straight | -20 to 500°C[-4 to 932°F]   | 0.75% or ±2.5°C(±4.5°F) | 2                      | φ15 (temp. sensing portion)   | 1.2 m       |
| 900 33  | Surface angled   | -20 to 500°C[-4 to 932°F]   | 0.75% or ±2.5°C(±4.5°F) | 2                      | φ15 (temp. sensing portion)   | 1.2 m       |
| 2459 07 | Bead TC          | -40 to 260°C[-40 to 500°F]  | 0.75% or ±2.5°C(±4.5°F) | 1200 (included cord)   |                               |             |

(90% response)  
NOTE: 900 30 is using polyimide to insulate from objects to be measured. Manufacturers of polyimide are announcing not to apply polyimide directly for food, internal and body fluid.

Temperature and Humidity Probe (900 01 / U; for TM20 only)

|                 | Humidity  | Temperature  |
|-----------------|---|--|
| Measuring range | 0 to 95% RH   | -10 to 50°C(°C only)                                 |
| Accuracy        | 20 to 80% RH: ±3% RH<br>0 to 20% RH, 80 to 90% RH: ±4% RH | 20°C: ±5°C: ±0.5°C<br>other than those above: ±0.7°C |
| Output          | 1 mV / % RH   | 1 mV / °C  |
| Response time   | 15 sec  | 15 sec   |

### Optional Accessories for TM10

| Product name                   | Model  |
|--------------------------------|--------|
| Standard needle probe          | 900 10 |
| High-speed needle probe        | 900 11 |
| Surface probe                  | 900 12 |
| Rounded end probe (for liquid) | 900 13 |
| Soft case                      | 930 10 |

### Optional Accessories for TM10/TM20

| Product name                            | Model  |
|---|--------|
| Non-contact probe                       | 900 03 |
| RS-232C cable for PC connection (9-pin) | 910 11 |
| Printer                                 | 970 10 |
| AC adapter for printer (Europe)         | 940 06 |
| AC adapter for printer (USA)            | 940 07 |
| Thermal paper for printer (10 rolls)    | 970 80 |
| RS-232C cable for printer connection    | 910 10 |

### Optional Accessories for TM20/TX10

| Product name  | Model                          |
|---|--------------------------------|
| Temperature probe (for type K)                          | 900 20/21/22/23/24/30/31/32/33 |
| Bead TC (for type K)                                    | 2459 07                        |
| K-shape connector                                       | 990 09                         |
| U-shape connector (for input voltage) (for TM20 only)   | 990 08                         |
| Extension cable (5 m)                                   | 2459 21                        |
| Extension cable (10 m)                                  | 2459 22                        |
| Soft case   | 930 12                         |
| Waterproof cover (5 per package) (for TM10, TM20, TX10) | 930 11                         |


NOTE: Please purchase commercially available thermocouples (Type-E/J/T), connectors and extension cables.

## External Dimensions

TM10  
TM20


Non-contact probe (900 03)

Unit: mm




TM10


Standard needle probe (900 10) / Rounded end probe (900 13) / Material: SUS316



High-speed needle probe (900 11) / Material: SUS316




Surface probe (900 12) / Material: SUS316




TM20  
TX10


900 20  
Material:  
SUS316




900 21  
Material:  
SUS316




900 22  
Material:  
SUS316




900 23  
Material:  
SUS316




900 24  
Material:  
SUS316




2459 07




900 30  
Material: SUS316




900 32  
Material: SUS316



900 31  
Material: SUS316



900 33  
Material: SUS316



900 01/U



**YOKOGAWA**  
Yokogawa M&C Corporation

World Wide Web site at  
<http://www.yokogawa.com/MCC>

### NOTICE

● Before using the product, read the instruction manual carefully to ensure proper and safe operation.

YOKOGAWA M&C CORPORATION  
International Sales Dept.

2-9-32 Nakacho, Musashino-shi, Tokyo, 180-8750 Japan  
Phone: +81-422-52-5716 Facsimile: +81-422-55-8954

Represented by:

YOKOGAWA CORPORATION OF AMERICA (U.S.A.)  
YOKOGAWA EUROPE B. V. (THE NETHERLANDS)  
YOKOGAWA ENGINEERING ASIA PTE. LTD. (SINGAPORE)  
YOKOGAWA AMERICA DO SUL LTDA (BRAZIL)  
YOKOGAWA MEASURING INSTRUMENTS KOREA CORPORATION (KOREA)  
YOKOGAWA AUSTRALIA PTY. LTD. (AUSTRALIA)  
YOKOGAWA BLUE STAR LTD. (INDIA)  
YOKOGAWA MIDDLE EAST E.C. (BAHRAIN)  
LTD. YOKOGAWA ELECTRIC (RUSSIAN FEDERATION)

Phone: +1-770-253-7000  
Phone: +31-334-64-1611  
Phone: +65-6241-9933  
Phone: +55-11-5681-2400  
Phone: +82-2-551-0660  
Phone: +61-2-9805-0699  
Phone: +91-80-227-1513  
Phone: +973-358100  
Phone: +7-095-737-7868

Facsimile: +1-770-251-2088  
Facsimile: +31-334-64-1610  
Facsimile: +65-6241-2606  
Facsimile: +55-11-5681-1274/4434  
Facsimile: +82-2-551-0665  
Facsimile: +61-2-9888-1844  
Facsimile: +91-80-227-4270  
Facsimile: +973-336100  
Facsimile: +7-095-737-7869

MCK-ES10

Subject to change without notice.  
All Rights Reserved. Copyright © 2000, Yokogawa M&C Corporation.

[Ed: 04/b]

Printed in Japan: Aug 2002(C)/3,000(YG)